Diaphragm Pumps for Air, Gases and Vapours

INNOVATIVE TECHNOLOGY WORLDWIDE





LABOPORT® Mini Diaphragm Vacuum Pumps

Technical features:

- 100% oil-free transfer
- Pure transfer, evacuation and compression
- Version for slightly aggressive or corrosive gases and vapours
- Maintenance-free
- Environmentally friendly
- High level of gas tightness.

Series LABOPORT® N 816.1.2 K_.18 Pumps

With fine control valve

and vacuum gauge (.45)

Series N 816.1.2 diaphragm pumps are double-head, dry-running devices used in a wide range of laboratory applications. They transfer and pump down without contamination.

The heart of these very compact pumps is a KNF structured diaphragm. This patented diaphragm was stress-optimized using the Finite Elements method. As a result, we were able to make the pumps smaller while increasing the service life of the diaphragm.

The pumps are available in various versions differing in the materials which contact the media.

Material in contact with the pumped media

Type/Order No.	Pump head	Diaphragm	Valves
N 816.1.2 KN.18	PPS	EPDM	EPDM
N 816.1.2 KN.45.18	PPS	EPDM	EPDM
N 816.1.2 KT.18	PPS	PTFE-coated	FFPM
N 816.1.2 KT.45.18	PPS	PTFE-coated	FFPM

.45 = Pump with fine control valve and vacuum gauge

Technical data:	N 816.1.2 KN.18 N 816.1.2 KN.45.18	N 816.1.2 KT.18 N 816.1.2 KT.45.18
Delivery (I/min) ¹⁾	30	30
Ultimate vacuum (mbar abs.)	100	160
Operating pressure	0.5	0.5

0.5 Connectors for tube ID 6 ID 6 Permissible gas and ambient temperature +5...+40 °C +5...+40 °C 230V/50Hz Mains 230V/50Hz Motor protection IP 20 IP 20 Power P₁ 100 W 100 W Operating current 0.6 A 0.6 A Weight 3.95 kg 3.95 kg **Dimensions** LxHxW (mm) 361/141/102 361/141/102

Motors with other voltages and frequencies on request.

With thermal switch and power fuse

Accessories and spare parts


Description	Details	Order No.
Fine control valve with vacuum gauge	suction side	056547
Spares kit	for N 816.1.2 KN	056315
Spares kit	for N 816.1.2 KT	056316

¹⁾ at atm. pressure


Diaphragm Pumps for Air, Gases and Vapours

Dimensions and performance characteristics


Pump down time for 20 I receiver




Performance



Pump down time for 20 I receiver



Performance



Dimensions (mm)

